

FUZZYSCAN A780 HC

2D 抗菌成像器



高性能的抗菌型 2D 条码扫描器，适合在注重卫生的环境内运用

在医院、诊所、实验室、药局、食品处理场、等环境中，工具都容易感染上周围的细菌。Cino 的 A780 HC 是专门为了该类环境所设计的高性能 2D 扫描器。拥有抗菌并且可消毒的外壳，此机种适合对卫生有严格标准的专业应用。此外，其优越的解码能力、坚固的构造、以及内置的振动器将为您带来上等的扫描体验。

- 可消毒的抗菌外壳
- 符合 JIS Z2801:2000 抗菌标准
- 可读取多种有挑战性或难以扫描的条码
- 高等的首次阅读率
- 全方向快速扫描
- 可读取智能手机屏幕上的条码
- 可承受自 2 m 高处跌落至水泥地面
- 拥有 Standard Range 以及 High Density 型号
- 明确的音响和视觉上反馈
- 选配的振动器能提供触觉式的反馈
- 可使用 iCode 履行配置
- 可使用 DataWizard 执行进阶的数据编排
- 可使用 DataWizard 开发系统安全机制

专注卫生的优良设计

可消毒的外壳

本机种的外壳可使用 Cino 推荐之清洁剂（参见以下产品规格）进行消毒，帮助您保持设备与环境的卫生。

含有抗菌添加剂

外壳使用含有银型无机抗菌剂的材料制作，在使用寿命时间内不会被磨去，并将持续保持抗菌效果。此材料有助于限制微生物在外壳上生长。

符合抗菌标准

此扫描器符合 JIS Z2801:2000 标准，适用于对环境卫生有严格标准的专业应用，比如医疗、制药、化妆品、食品工业、医学实验室、等等。

扫描您所有的需求

卓越的成像平台

Cino 的 FuzzyScan 成像平台结合了图像处理、电光学、计算架构和条码解码的最新进展。其也利用机器学习算法来增强动态曝光控制、模式发现、图像处理以及历史控制。

此卓越的平台内置于 Cino 扫描器中，提高数据捕获的性能。

克服难以读取的条码

采用 FuzzyScan 成像平台，此扫描器可以捕获多种有挑战性或有问题的条码，例如：扭曲、脏污或损坏的条码，或者在低光度萤幕上的电子条码。



医院



实验室



药局

满足不同的扫描需求

本机种的『Standard Range』型号能满足大多数的扫描需求。此型号让您可以快速读取一般或高密度的条码，因此适合多种的商业应用。若您的应用是针对非常小的高密度 2D 条码（例如：电子零件、珠宝标签或医疗设备等的小型条码），您可以选择本机种的『High Density』型号。Cino 提供不同的选项来协助使用者完成他们的扫描工作。

最佳用户体验

轻松、容易的扫描

此扫描器具有全方位读取功能。其操作简单、容易。无需先与条码对齐并可直接进行扫描，让您可以更快地完成工作。

精确的瞄准灯加快您的扫描速度

透过锐利、圆形的 LED 光束，本成像器能让您更快、更准确地瞄准条码。另外，其也会投射光亮的背景照明，因此在低灯光的环境下也能快速地读取条码。

清晰的音频、视觉和触觉反馈

此机种具有可调节音量的蜂鸣器以及多色的 LED 指示。内置振动器能提供触觉式的读取确认。当成像器的响声会造成困扰时，例如在患者休息的病房或图书馆内，振动器是理想的反馈机制。在背景噪音可能会淹没响声的环境中（例如，制造工厂），振动器也能发挥其实用性。这些功能一起给您带来更优良的扫描体验。

坚固并且符合人体工学的结构

本机种的坚固外壳使其能够承受从 2.0 m 的高处跌落至水泥地面，提供良好的保护功效。它也结合了时尚外观设计与人体工学。其手柄给以自然的抓握，在执行重复性的工作时，能助于减少用户疲劳。

优越的附加值

简化的配置过程

iCode 是个配置条码并且能包含多种命令。扫描一个 iCode 就能让您一次完整地设定多项参数。只需在 FuzzyScan PowerTool 中选择适用的参数，然后点击『iCode』按钮即能产生出一个全面性的配置条码。

自订功能

透过 DataWizard，您可以编写自制的配置程式，并使用该程式来设定 Cino 成像器，使其执行进阶的数据编排，或参与系统保卫工作。程式语言和 BASIC 相似，易于有经验的程序员学习。此独特的功能包含在 FuzzyScan PowerTool 内，提供给 Cino 客户免费使用。

进阶的数据编排

Cino 成像器能按照您自订程式内的指令来进行数据编排，从而分担主机的工作。例如：解析驾驶执照的条码数据、添加前导码或后缀、等等。

系统安全

为了防护主机系统，用户可以在系统内设定连接前的验证密码流程。透过 DataWizard，用户可以编写能够生产出密码的程式，并在受允许的成像器上安装该程式。此机制将防止未受批准的仪器与主机系统连接。

SPECIFICATIONS

Performance Characteristics

Image Sensor	1280 x 800 Pixels
Print Contrast	15% minimum reflectance difference
Light Source	660nm red LED
Imager Field of View	41.5° H x 25.9° V
Minimum Resolution	HD 2.4mil Code 39, 4.5 mil DM SR 2.7mil Code 39, 4.8 mil DM
Reading Range *1	HD 13 mil (0.33mm) UPC/EAN up to 14.5" SR 13 mil (0.33mm) UPC/EAN up to 23.6"
Roll, Pitch, Skew	Roll: 360°; Pitch: ± 75°; Skew: ± 65°
Motion Tolerance	Up to 617 cm/s (243 in/s)
Configuration Setup	FuzzyScan Barcode commands FuzzyScan iCode FuzzyScan PowerTool FuzzyScan Serial Command
Data Processing	DataWizard
User Interfaces	3 LEDs for power, good read and status indications Programmable beeper Built in vibration
Image Capture	BMP

Electrical Characteristics

Operating Voltage	5VDC ± 10%
Operating Current	Operating : Typical 395 mA @5VDC Standby : Typical 220 mA @5VDC
Antimicrobial Additives	Silver inorganic antimicrobial agent

Physical Characteristics

Dimensions	93.5 mm (L) x 71 mm (W) x 160 mm (D) 3.68 in. (L) x 2.79 in. (W) x 6.29 in. (D)
Weight	150g (cable excluded)
Color	Healthcare White
Host Interfaces	USB HID (USB Keyboard) USB VCOM (USB COM port emulation) USB OEM POS Standard RS232

1. The Reading Range are measured under Cino's test environmental condition.
2. Codablock F, Code 16K, Code 49, Chinese Sensible (Han Xin) Code and OCR are available upon request.
3. Don't stare into the LED beam.

Supported Symbolologies

1D Linear Codes	Code 39, Code 39 Full ASCII, Code 32, Code 128, GS1-128, Codabar, Code 11, Code 93, GS1 DataBar, Standard & Industrial 2 of 5, Interleaved & Matrix 2 of 5, IATA, UPC/EAN/JAN, UPC/EAN/JAN with Addendum, Telepen, MSI/Plessey & UK/Plessey
2D Codes *2	PDF417, Micro PDF417, Composite Codes, DataMatrix, MaxiCode, QR Code, MicroQR, Aztec, Codablock F, Code 16K, Code 49, Chinese Sensible (Han Xin) Code
Postal barcodes	Australian Post, US Planet, US POSTNET, Japan Post, Posi LAPA 4 State Code, German Post, British Post, Intelligent Mail, Korean Post, Dutch KIX Post, China Post
OCR *2	OCR-A/B, MICR-E13B, US Currency Serial Number

User Environment

Drop Specifications	Withstands multiple drops from 2m (6.6ft) to concrete
Environmental Sealing	IP52
Operating Temperature	-10 °C to 50 °C (14 °F to 122 °F)
Storage Temperature	-40 °C to 70 °C (-40 °F to 158 °F)
Humidity	0% to 95% relative humidity, non-condensing
Ambient Light Immunity	0 ~ 106,000 lux
ESD Protection	Functional after 15KV discharge
Recommended cleaning solutions	Gentle dish soap water or alcohol solvent

Safety & Regulatory

EMC	CE, UKCA, FCC, BSMI, RCM, KC, VCCI
Safety *3	LED Eye Safety IEC 62471/EN 62471, Exempt Group
Environmental	Compliant with RoHS 2.0 and REACH
Antimicrobial	JIS Z2801 : 2000

Accessories

Cables	RS232 Serial Cable USB-A Cable USB-C Cable USB Power Cable
Others	US100 SmartStand Universal Holder Power Supply Unit (5VDC, 2A outlet)

